

CECO Mefiag


A Division of CECO Environmental

BULLETIN 906
SETHCO
BAG
FILTERS

DBG-5



DBG-1



Filter bags are easy to replace.

1. Remove cover.
2. Pull out used filter bag.
3. New filter bag fits quickly and securely into chamber.



High-strength reusable bag filters

HIGH STRENGTH REUSABLE BAG FILTERS

Filter bags are constructed of polypropylene felt. The high strength felt is produced by the kneading of two layers of polypropylene fibers into a supporting scrim. This provides depth filtration and a higher solids-loading capacity than an equivalent area of mesh fabric. The one-piece design of the filter bag provides a positive seal when locked into the chamber, ensuring no contaminant by-pass and high-efficiency filtration.

FOR CHAMBER MODEL	MATERIAL	NOMINAL MICRON RATING	CODE NUMBER
#A SIZE (0.5 Sq. Ft.)			
DBG-1/2	POLYPROPYLENE	1,10,25,50	906-10FP3*
#B SIZE (1 Sq. Ft.)			
DBG-1	POLYPROPYLENE	1,10,25,50	906-20FP3*
#C SIZE (1.5 Sq. Ft.)			
DBG-1 1/2	POLYPROPYLENE	1,10,25,50	906-30FP3*
#2 SIZE (1.8 Sq. Ft.)			
DBG-2	POLYPROPYLENE	10,25,50	906-13P6VG*
	POLYPROPYLENE	1,3,100	906-13P6VG*
	POLYPROPYLENE	300	906-13P6VG300
#3 SIZE (3 Sq. Ft.)			
DBG-3	POLYPROPYLENE	10,25,50	906-23P6VG*
	POLYPROPYLENE	1,3,100	906-23P6VG*
	POLYPROPYLENE	300	906-23P6VG300
#5 SIZE (5.2 Sq. Ft.)			
DBG-5	POLYPROPYLENE	10,25,50	906-40P6VG*
	POLYPROPYLENE	1,3,100	906-40P6VG*
	POLYPROPYLENE	300	906-40P6VG300*
(0.5 Sq. Ft.)			
SBC-1/2	POLYPROPYLENE	1,10,25,50	906-09FP3*
(1 Sq. Ft.)			
SBC-1	POLYPROPYLENE	1,10,25,50	906-19FP3*
(1.5 Sq. Ft.)			
SBC-1 1/2	POLYPROPYLENE	1,10,25,50	906-29FP3*
(2.75 Sq. Ft.)			
SBC-3	POLYPROPYLENE	10,25,50	906-24FP6*
	POLYPROPYLENE	1,3,100	906-24FP6*
(4 Sq. Ft.)			
SBC-4	POLYPROPYLENE	10,25,50	906-34FP6*
	POLYPROPYLENE	1,3,100	906-34FP6*

*Insert micron rating.



A Division of CECO Environmental

700 Emlen Way • Telford, PA 18969

Phone: 215.723.8155

Email: infofhs@onececo.com

www.cecoenviro.com